


NAD SERVICE MANUAL


**MONITOR SERIES
5100
COMPACT DISC PLAYER**

SAFETY INFORMATION

DANGER—Invisible laser radiation when open and interlock failed or defeated.
AVOID DIRECT EXPOSURE TO BEAM.





CAUTION—HAZARDOUS LASER AND ELECTROMAGNETIC RADIATION WHEN OPEN AND INTERLOCK DEFEATED
ATTENTION—RAYONNEMENT LASER ET ELECTROMAGNETIQUE DANGEREUX SI OUVERT AVEC L'ENCLENCHEMENT DE SECURITE ANNULE



THIS PRODUCT COMPLIES WITH DHHS RULES 21 CFR SUBCHAPTER J PART 1040.10 AND 1040.11 AT DATE OF MANUFACTURE.
MANUFACTURED: BEY

CAUTION

CAUTION — INVISIBLE LASER RADIATION WHEN OPEN AND INTERLOCKS DEFECTED. AVOID EXPOSURE TO BEAM.
VORSICHT! UNSICHTBARE LASERSTRÄHLUNG TRITT AUF,
WENN DECKEL GEÖFFNET UND WENN
SICHERHEITSVERriegelung UBERBRÜCKT IST.
NICHT DEM STRAHL AUSSETZEN!
WARNING — OSYNLIG LASERSTRÄLLNING NAR DENNA DEL
AR ÖPPNAD OCH SPARR AR URKOPPLAD.
STRÄLEN AR FARLIG.
ADVARSEL — USYNLIG LASERSTRALING VED ÅBNING NAR
SIKKERHEDSAFBRYDERE ER UDE AF FUNKTION
UNDGÅ UDSÆTTELSE FOR STRALING.





The lightning flash with arrowhead, within an equilateral triangle, is intended to alert the user of the presence of uninsulated "dangerous voltage" within the product's enclosure; that may be of sufficient magnitude to constitute a risk of electric shock to persons.



The exclamation point within an equilateral triangle is intended to alert the user of the presence of important operating and maintenance (servicing) instructions in the literature accompanying the appliance.


REAR PANEL

1. Fixed-level output jacks.
2. Variable-level output jacks.
3. AC line cord.



FRONT PANEL

1. Power on/off.
2. Headphones.
3. Disc drawer.
4. Open/Close.
5. Reset.
6. Time display selector.
7. Repeat.
8. CDR (controlled dynamic range).
9. Skip forward/back.
10. Scan forward/back.
11. Headphone volume.
12. Play/Pause.
13. Memory enter.
14. Program mode.
15. Delete mode.
16. Display.



Contents

	Page
CAUTIONS ON REPLACEMENT OF PICK-UP	4
SPECIFICATIONS	4
ALIGNMENT PROCEDURES	5
ACTION FLOW CHART	9
TROUBLE SHOOTING GUIDE	10
WIRING DIAGRAM	15
BLOCK DIAGRAM	17
SCHEMATIC AND PCB LAYOUT	19
EXPLODED VIEW AND PARTS LIST	25
SCHEMATIC DIAGRAM	33
THE DIFFERENCE OF PICK-UP HEAD	35

Cautions on Replacement of Pick-up

1. Do not touch the terminals on the pick-up with your hand when removing the laser pick-up.
2. Cover the working bench with a conductive mat which is also grounded.
3. Before proceeding job, always touch the conductive mat or ground lead with your both hands to discharge electric charges developed on your body.
4. To protect your vision do not expose your eyes to the direct laser light. The beam is focused at a distance of 2 mm from the lens.

SPECIFICATIONS (at Fixed Output)


	Nominal	Limit	Unit	
Decoding	: 16-bit linear,two channels			Power consumption
Frequency response 20 Hz-20 kHz	+0.2 -0.5	+1.0 -1.0	dB	Dimensions : Width 435 mm (17.13 in.) Height 75 mm (2.95 in.) Depth 285 mm (11.22 in.)
De-emphasis error	+0.5 -1	+1.0 -2.0	dB	Net weight : 5.1 kg (11.2 lb)
Output level at 0 dB	: 2 volts±0.7	±1.0	dB	
Harmonic Distortion	: 0.004	0.01	%	
W/20 kHz L.P.F at 1 kHz 0 dB				A : USA A1: CANADA
Signal-to-Noise Ratio	: 99	90	dB	B : U.K. B1: AUSTRALIA/N.Z.
W/20 kHz L.P.F				C : EUROPE & OTHERS
Channel Separation	: 88	80	dB	C1: W.GERMANY
W/20 kHz L.P.F at 1 kHz Channel Balance at 1 kHz 0 dB	: 0.5	1.0	dB	C2: G.P.M.
Wow and Flutter	: Unmeasurable (quartz crystal accuracy)			

ALIGNMENT PROCEDURES

Measuring instruments

Oscilloscope (Which has a bandwidth of 50 MHz or greater)
 Audio frequency oscillator (AF-OSC)
 Laser power meter (LEADER LPM-8000 or equivalent)
 AC voltmeter (ACVM) – dual channel meters
 Frequency counter (FC)
 Jitter meter
 Test Disc A: YEDS 7 (SONY)
 Test Disc B: YEDS 18 (SONY)
 Jigs: Filter (See Fig. A)
 Special tool (See Fig. F)

INPUT Side




SW1: For diffraction grating and EF balance adjustments
 SW2: Focus gain and TRACKING gain switch
 SW3: BPF ON/OFF switch

[Fig. A]

Main P.C.B. test points

Adjustment Jig (with internal filter) connect the filter in Jig before measurement.




[Fig. B]

Step 1 Confirmation of Laser Output

- 1) Do not load the disc.
- 2) Apply the laser power meter sensor to the pick-up head as shown in Fig. C.
- 3) Operate from OPEN to CLOSE.
- 4) Measure the laser output during the 6 seconds of FOCUS search mode.

Rating laser output: 0.12 mW to 0.36 mW



[Fig. C]

Step 2 Confirmation of Focus Actuator Operation


Oscilloscope Setting

DC coupling

0.1 V/div when 10:1 probe is used

0.5 sec/div or 1 msec/div time

- 1) Do not load the disc.
- 2) Connect the oscilloscope to TP003 [R] and TP016 [GND] points (See Fig. B).
- 3) Press the CLOSE key.
- 4) During 6 seconds of FOCUS search, confirm that the wave-form is as shown in Fig. D.
- 5) Confirm that the pick-up head's objective lens moves smoothly between the lowest and highest points.



[Fig. D]

Step 3 Adjustment of Diffraction Grating

Caution:

The oscillogram produced during this adjustment procedure can only be displayed for approx 10 sec. After which time the TER signal will automatically go out. Wave-form observation and adjustments should be carried out as quickly as possible. In order to display the wave-form use the following procedure.

Oscilloscope Setting

DC coupling

10 mV/div when a 10:1 probe is used

5 to 20 msec/div time

- 1) Connect the oscilloscope to TP007 [TER] and TP016 [GND] test points.

- 2) Load the test disc. (Test Disc: B)

- 3) Press the CLOSE key (Allow the lead in data on the disc to be read).

- 4) Press the PLAY/PAUSE key twice then in PAUSE mode.

- 5) Put SW1 on the test jig to the ON position (In this position test points TP009 [TDI] and TP002 [Q] will be shorted together) and the wave-form as shown in Fig. E should be displayed on the oscilloscope. In order to prevent the display from going out, put the SW1 OFF and put the SW1 ON again.

- 6) Appear the wave-form like Fig. E on the oscilloscope.

- 7) Using the special tool (See Fig. F) carry out the adjustment (See Fig. G) for maximum amplitude of the displayed signal (See Fig. E).

Rating Signal TER \geq 250 mVp-p

* If the disc stops rotating and "d i" is displayed on the LED display eject the disc and go back to step 5 - 2).

Oscilloscope Setting Conditions

AC coupling


50 mV/div when 10:1 probe is used

0.2~0.5 μ sec/div time

- 8) Put SW1 to the OFF position (TP009 [TDI] and TP002 [Q] points open)


- 9) Connect the oscilloscope to test point TP015 [HS] and TP016 [GND].

- 10) Confirm that [HS] (eye-pattern) signal is displayed on the oscilloscope (See Fig. H).




[Fig. E]

Special tool for MLP-10F2




[Fig. F]


Less than $\pm 5^\circ$



[Fig. G]



This portion is referred to as the eye pattern.



The abnormal eye pattern has less distinct lines and smaller amplitude than that of the good wave-form.

[Fig. H]


Way of lissajous's figure

Oscilloscope Setting


X input → [E] signal: 5 mV/div when 10:1 probe is used
Y input → [HS] signal: 50 mV/div when 10:1 probe is used
MODE → X - Y

- 1) Connect the buffer amplifier, as shown in Fig. I between the point [E] and the X input oscilloscope.
- 2) Connect the Y input of point TP015 [HS] and oscilloscope.
- 3) Set the disc in play mode. (Test Disc: B)
- 4) Turn ON the Put SW1. (Short-circuit TP002 [Q] and TP009 [TDI])
- 5) Adjust the special tool until the wave-form is like Fig. J.

Buffer Amplifier



[Fig. I]



[Fig. J]

Step 4 Adjustment of EF Balance

Oscilloscope Setting


DC coupling

10 mV/div when 10:1 probe is used

5 to 20 msec/div time

- 1) Same as from 1) to 6) of step 3.
- 2) Adjust SVR 102 and do like Fig. K.

Rating DC offset — Less than ± 15 mV



[Fig. K]

Step 5 Adjustment of Focus Gain

- 1) Connect the filter and measuring instruments, as shown in Fig. A. Apply 800 Hz, 4.5 Volts RMS signal from the AF oscillator to AF-OSC terminal on Jig.
- 2) Set the SW3 to OFF.
- 3) Set the SW2 to F (FOCUS).
- 4) Load the disc. (Test Disc: B)
- 5) Press the PLAY key.
- 6) Set the SW3 to ON.
- 7) Read the AC voltmeter (CH1: EFO, CH2: ER), adjust SVR106 (FOCUS GAIN) so that they satisfy the rating.

Rating: $ER = (EFO + 14 \text{ dB}) \pm 2 \text{ dB}$

Step 6 Adjustment of Tracking Gain

- 1) Connect the filter and measuring instruments, as shown in Fig. A. Apply 800 Hz, 100 mVrms signal from the AF oscillator to AF-OSC terminal on Jig.
- 2) Set the SW3 to OFF.
- 3) Set the SW2 to T (TRACKING).
- 4) Load the disc. (Test Disc: B)
- 5) Press the PLAY key.
- 6) Set the SW3 to ON.
- 7) Read the AC voltmeter (CH1: ETE, CH2: EQ) adjust SVR103 (TRACKING) so that they satisfy the rating.

Rating: $ETE = (EQ + 11 \text{ dB}) \pm 3 \text{ dB}$


Step 7 Adjustment of Focus Offset

Oscilloscope Setting

DC coupling

10 mV/div range

- 1) Do not load the disc.
- 2) Connect the oscilloscope through the filter shown in Fig. L to TP003 [R] and TP016 [GND] points.
- 3) Do not press the PLAY key.
- 4) Adjust SVR 105 until the level is within $0 \text{ V} \pm 10 \text{ mV}$ DC.



[Fig. L]

Step 8 Adjustment of Tracking Offset

Oscilloscope Setting

DC coupling

10 mV/div range

- 1) Do not load the disc.
- 2) Connect the oscilloscope through the filter shown in Fig. L to TP002 [Q] and TP016 [GND] points.
- 3) Do not press the PLAY key.
- 4) Adjust SVR 101 until the level is within $0 \text{ V} \pm 10 \text{ mV DC}$.

Step 9 Confirmation of Kick Gain

Oscilloscope Setting

DC Coupling


CH1 → TP007 [TER] terminal, 0.1 V/div

CH2 → TP011 [TRHD] point, 5 V/div

TRIGGER MODE: CH2

0.2 msec/div time

- 1) Connect the oscilloscope of CH1 to TP007 [TER] terminal on Jig.
- 2) Connect the oscilloscope of CH2 to TP011 [TRHD] point.
- 3) Load the disc. (Test Disc: B)
- 4) Press the PLAY key.
- 5) Press the Fast Forward key.
- 6) Confirm the wave-form, as shown in Fig. M.
- 7) Press the Reverse key.
- 8) Confirm the wave-form, as shown in Fig. M.



[Fig. M]

Step 10 Adjustment of VCO

- 1) Connect the Frequency Counter to TP016 [GND] and TP012 [CK]. (See Fig. B)
- 2) Short the TP015 [HS] and TP016 [GND].
- 3) Adjust L201 until the VCO is $4.3218 \text{ MHz} \pm 10 \text{ kHz}$.

Step 11 Adjustment of THD


- 1) Connect the distortion meter to the output.
- 2) Load the disc. (Test Disc: A)
- 3) Press the play key.
- 4) Press the skip key and keep it pressed until the display shows Track No. 20.
- 5) Adjust the SVR 301 so that the output distortion will be minimum.

NOTE: If the input to the distortion meter is not large enough for measurements, use an amplifier of about 30 to 40 dB gain between the CD output and the meter input.


Step 12 Adjustment of CDR

- 1) Connect the AC voltmeter to the output.
- 2) Load the disc. (Test Disc: A)
- 3) Press the play key.
- 4) Press the skip key and keep it pressed until the display shows Track No. 19.
- 5) Adjust the SVR 401 (left channel) and SVR 402 (right channel) so that the output level with the CDR switch set to ON is 3 dB higher than when the CDR switch is OFF.


ACTION FLOW CHART





TROUBLESHOOTING GUIDE




2.









4.



WIRING DIAGRAM(Component side)





BLOCK DIAGRAM



SCHEMATIC AND PCB LAYOUT(Foil side)


LED PCB ASSY



SL9406-20





LN513RKS





Pin Connection

Pin No.	Address	Pin No.	Address
1	Colon Common (No Pin)	12	D ₄ Common
2	a	13	a
3	b	14	g
4	c	15	(No Pin)
5	d	16	(No Pin)
6	e	17	Upper Colon
7	f	18	D ₂ Common (No Pin)
8	dp	19	b
9	dp	20	f
10	(No Pin)	21	D ₁ Common
11	(No Pin)	22	(No Pin)

OPERATION PCB ASSY





VOLUME PCB ASSY





POWER SUPPLY PCB ASSY

(A,A1) Vers on
for USA
CANADA only
(B,B1,C,C1,C2)
Version for
UK/AUSTRALIA,
NZ,G,P,M
W GERMANY
EUROPE, OTHERS



HEADPHONE PCB ASSY



MAIN PCB ASSY

WARNING:
Parts marked with the symbol  have critical characteristics.
Use ONLY replacement parts recommended by the manufacturer.

CAUTION:
Before returning the unit to the customer, make sure you make either (1) a leakage current check or (2) a line to chassis resistance check. If the leakage current exceeds 0.5 milliamper, or if the resistance from chassis to either side of the power cord is less than 500 k ohms, the unit is defective.

500 K ohms the unit is defective.
WARNING - DO NOT return the unit to the customer until the problem is located and corrected.

CAUTION:
THOSE FUSES WITH SYMBOL MARKS ARE

ATTENTION:
LES FUSIBLES MARQUES -


250 V
400 mA

 SONT DE TYPE A.

FUSION RAPIDE, UTILISER UN FUSIBLE DE
RECHANGE DE TYPE DE 400 mA 250 V.


101

10



EXPLODED VIEW AND PARTS LIST


Main Unit



Parts marked with * vary according to destinations.
For details, refer to the classify parts list.

REF. NO.	Q'TY	PART NO.	DESCRIPTION
COILS			
PT001	1	NPT-K0104	POWER TRANSFORMER
MISCELLANEOUS			
J008	1	R-020-15	CABLE ASS'Y
J009	1	R-027-15	TERMINAL WITH WIRE
J015	1	R-030-15	CABLE ASS'Y
1M 1	1	BK2033-1	FRONT PANEL
1M 2	1	BK10220	DISPLAY FRAME
1M 4	1	BK3032	FRONT GLASS
1M 5	1	BK4158	FILTER
1M 7	1	62-1111-1-0	PUSH BUTTON
1M 8	1	N44956-GY	PUSH BUTTON
1M 9	2	N44957-BK	PUSH BUTTON
1M10	2	N44956-BK	PUSH BUTTON
1M11	1	N44988-RD	PUSH BUTTON
1M13	1	BK3025	KNOB (POTENTIOMETER)
1M15	1	BK3023-1	TRAY PANEL
1M17	1	BK2031	CABINET
1M18	1	DK2037	REAR PANEL
1M19	1	DK10218	BOTTOM CHASSIS
1M20	4	NO.7102A	FOOT
1M22	2	NA5346	DISC CUSHION
1M23	2	BK4176	DISC CUSHION
2M 1	1	BK4068	FITTINGS (SWITCH)
2M 2	1	N42281A	SHAFT (SW)
2M 3	1	NO.2015	ANT. HOLDER
2M 4	2	BK4148	FITTINGS R (CD)
2M 5	1	BK4147	FITTINGS F (CD)
2M 6	4	BK4157	HOLDER
2M 7	4	BK4078	HOLDER
2M 8	2	M2435	FITTINGS (P.C.B.)
2M 9	1	BK4149	JACK HOLDER
2M10	1	KGL5-3S	SPACER
2M11	2	KGP5-3.5S	SPACER
2M12	4	7900199	INSULATION RUBBER B
2M13	12	H4459	KNOB SPRING
2M14	1	N4460	KNOB SPRING
2M15	1	BK4141	EARTH SPRING
2M16	2	BK4196	CUSHION
2M17	2	BK4198	CUSHION
2M18	1	BK4175	SPACER
2M19	2	BK4180	CUSHION TAPE
2M20	1	BK4181A	SHEET A
2M21	1	BK4182A	SHEET B
2M23	3	VJR-3	SNAKE LUG
2M24	1	CS-5	CLIP
2M25	4	BK4145	SPRING
2M26	2	BK4177	WASHER
2M27	2	BK4198	CUSHION
2M30	1	BK4160	PVC PLATE
3M 1	1	BK4150	INNER CARTON
3M 3	2	BK1023	PACKING PAD
3M 4	1	H44894	TAPE+PACKING MATERIAL
3M 7	1	PC-046	RCA PIN CORD ASS'Y
3M 8	1	N40687	POLYETHYLENE BAG (ACCESSORIES)
3M 9	1	ON-K040	INSTRUCTION MANUAL
3M10	1	N44687	CAUTION SHEET, POLARIZED PLUG
3M11	1	N44525	LABEL, FUSE
3M12	1	BK4072	SHOOT SHIPPING SCREW
3M14	1	BK4082A	FDA LABEL LASER CAUTION
3M15	1	BK4091A	CSA LABEL LASER CAUTION
3M17	2	N44521	LABEL, CAUTION
3M20	1	BK4159	PROTECTION SHEET
3M21	1	H41866-2	POLYETHYLENE BAG (UNIT)
3M23	1	HAD-WC2A	CARD WARRANTY REGISTRATION
3M24	1	BK4135	LABEL, WARNING
3M25	1	H44934A	LABEL, UL
3H26	1	BK3035	SAFETY INSTRUCTION SHEET
4H 1	3	TPH-30X08-B	TAP SCREW P, ROUND HEAD, B
4H 3	1	2THX30	TOOTHED WASHER (B)
4H 4	2	TPS-30X08-Y	TAP SCREW P, FLAT HEAD, Y
4H 5	4	TPH-30X08-B	TAP SCREW P, ROUND HEAD, B
4H 6	1	ZC+10X30X10-2B	TAP SCREW, WASHER FACED, B
4H 8	3	TPH-30X08-B	TAP SCREW P, ROUND HEAD, B
4M 9	2	TPS-30X10-Y	TAP SCREW P, FLAT HEAD, Y
4M10	2	2THX40-U	WASHER
4M11, M12	6	TSC-30X08-Y	TAP SCREW S, WASHER FACED, Y
4M13	4	T5B-30X08-Y	TAP SCREW S, BIND HEAD, Y
4M14	2	T5B-30X05-Y	TAP SCREW S, BIND HEAD, Y
4M15	2	T5B-40X08-Y	TAP SCREW S, BIND HEAD, Y
4M16	2	2AU-25B	REINFORCEMENT (P.T.)
4M17	2	ISO-30X08-B	TAP SCREW S, BIND HEAD, B
4M18	4	TSC-30X08-Y	TAP SCREW S, WASHER FACED, Y
4M19	2	T5B-30X08-Y	TAP SCREW P, ROUND HEAD, Y
4H20	2	TPH-30X10-R	TAP SCREW P, ROUND HEAD, R
4H22	2	SSP-30X08-Y	SCREW, PAN HEAD, Y
4H25	4	TPH-30X08-B	TAP SCREW P, ROUND HEAD, B
4H26	1	TSC-30X08-B	TAP SCREW S, WASHER FACED, Y
4H27	1	TSS-30X08-Y	TAP SCREW S, FLAT HEAD, Y
4H28	3	T5B-30X06-B	TAP SCREW S, BIND HEAD, B
4H29	1	TPH-30X08-B	TAP SCREW P, ROUND HEAD, B
5M 2	4	2AWX0840-05-B	PLAIN WASHER, B
5M 3	4	TSD-40X06-B	TAP SCREW S, BIND HEAD, B
5M 4	2	T5B-30X08-B	TAP SCREW S, BIND HEAD, B
5M 6	1	TSC-30X06-Y	TAP SCREW S, WASHER FACED, Y
5H 8	1	TSU-30X08-B	TAP SCREW S, BIND HEAD, B
5M10	2	TSC-30X08-Y	TAP SCREW S, WASHER FACED, Y
5M11	1	2TWX40-U	WASHER
5M13	4	T5B-30X10-Y	TAP SCREW S, BIND HEAD, Y
5M14	4	BK4093	SPECIAL SCREW
5M16	1	3TWX30-U	WASHER
5M18	1	TPS-30X12-N	TAP SCREW P, FLAT HEAD, N
5M19	1	2TWX50-U	WASHER
5H21, H22	2	T5B-30X05-Y	TAP SCREW S, BIND HEAD, Y
5H24	2	TPH-30X08-B	TAP SCREW P, ROUND HEAD, B
5M29, M30	2	T5B-30X05-Y	TAP SCREW S, BIND HEAD, Y
17E13	5	OSH-1625-MP	HEAT SINK
17E14	1	SH-1230	HEAT SINK
22E 1	1	RC-1001-C1	REMOTE CONTROL TRANSMITTER
22E 3	1	UM-3-2	BATTERY
22E 5	1	DM1532280	CD MECHANISM
22E16	1	ACC-039E3-4EC1	LINE CORD
22E19	1	SR-4N-4	CORD STOPPER
22E20	2	NO.5167	CORD CLAMP
22E21, E23	5	BK-1	CORD CLAMP

CD Player Mechanism



REF. NO.	Q'TY	PART NO.	DESCRIPTION
1	1	7910635	BASE MECHANISM
2	1	7910637	PIN HEAD FEED
3	1	7910638	PIN LOADING
4	1	7900181	LOADING MOTOR ASSY
6	4	7910659	SCREW M2L=4W/SPRING WASHER
7	1	7910642	WORM GEAR W/PINION
8	1	7910643	WASHER
9	1	7900182	FEED MOTOR ASSY
11	2	7910660	SCREW M2L=4W/SPRING WASHER
12	3	7910657	TAPPING SCREW WHI=8
13	1	7910650	FINAL GEAR
14	1	7910651	BELT RUBBER
15	1	7910648	PULLEY B
16	1	7910649	GEAR MAIN
17	1	7900074	MOTOR DISC
18	1	7910639	TURN TABLE
19	1	7910661	LEAF SWITCH 2 POLES
20	1	7900179	LEAF SWITCH MONO POLE
21	1	MLP-10F2	PICK UP HEAD
22	1	7910646	RACK B
23	2	SSPS2+26x08-Y	SCREW M26L=8W/SPRING WASHER
24	2	7910644	FEEDING SHAFT
26	1	7910627	CLAMPER ARM
27	1	7910628	CLAMPER DISC
28	1	7900127	FIXING PLATE
29	1	7900093	BUSHING CLAMP ARM
30	2	7900130	SCREW TAPPING
31	1	7910630	SPRING TENSION
32	1	7910631	TRAY DISC
33	1	7900166	TRAY SUB LEFT
34	1	7900167	TRAY SUB RIGHT
35	2	7900168	TRAY SUB TRAY
36	4	7910658	TAPPING SCREW 1=4
37	2	7900005	TAPPING SCREW
38	1	7900175	TRAY ASSY
39	1	7910647	MECHA BASE ASSY

MAIN PCB ASSY

REF. NO.	Q'TY	PART NO.	DESCRIPTION
<u>P.C.B. BOARD</u>			
IE 1	1	MAIN-K032A	PRINTED CIRCUIT BOARD
<u>SEMICONDUCTORS</u>			
D101	1	1SS133	DIODE
D102	1	MA27WA	DIODE
D103~110	8	1SS133	DIODE
D201	1	SVC211SP-B,C	DIODE
D202~207,	12	1SS133	DIODE
301~401,			
402~451~			
▲ D601~608	8	IN4002	DIODE
D609~610	2	1SS133	DIODE
Q101~103	3	2SC3311A-R,S	TRANSISTOR
Q104	1	2SD1225M-R	TRANSISTOR
Q105	1	2SB8909M-R	TRANSISTOR
Q106	1	2SB544-F	TRANSISTOR
Q107	1	2SA1309A-R,S	TRANSISTOR
Q108,109,	3	2SC3311A-R,S	TRANSISTOR
201			
Q202	1	2SA1309A-R,S	TRANSISTOR
Q203	1	2SC3311A-R,S	TRANSISTOR
Q204,205	2	2SA1309A-R,S	TRANSISTOR
Q206	1	2SC3311A-R,S	TRANSISTOR
Q207	1	2SA1309A-R,S	TRANSISTOR
Q208	1	2SC3311A-R,S	TRANSISTOR
Q209	1	2SD400-F	TRANSISTOR
Q210	1	2SC3311A-R,S	TRANSISTOR
Q211~214	4	2SA1309A-R,S	TRANSISTOR
Q215~218	4	2SC3311A-R,S	TRANSISTOR
Q301~306	6	2SC2878-A,B	TRANSISTOR
Q307	1	2SC3311A-R,S	TRANSISTOR
Q401~402	2	2SC1815-BL	TRANSISTOR
Q403~404	2	2SK363-BL	TRANSISTOR
Q405~406	2	2SC1815-BL	TRANSISTOR
Q407~408	2	2SA1015-Y	TRANSISTOR
Q451	1	2SA1309A-R,S	TRANSISTOR
Q452	1	2SC3311A-R,S	TRANSISTOR
Q453	1	2SA1309A-R,S	TRANSISTOR
Q454	1	2SC3311A-R,S	TRANSISTOR
Q455~458	4	2SC2878-A,B	TRANSISTOR
Q601	1	2SD400-F	TRANSISTOR
Q602	1	2SB544-F	TRANSISTOR
Q603	1	2SA1115-E,F	TRANSISTOR
Q604	1	2SD400-F	TRANSISTOR
Q605	1	2SC3311A-R,S	TRANSISTOR
Q606	1	2SB544-F	TRANSISTOR
Q607	1	2SA1309A-R,S	TRANSISTOR
IC191	1	XC488A0	IC
IC102	1	M54641L	IC
IC103	1	STA341M	IC
IC201	1	YM3616	IC
IC202	1	LC3517AM-15	IC
IC203	1	NJM2068S-D	IC
IC204	1	BA614	IC
IC205	1	BA618	IC
IC206	1	LC6526C-3164	IC
IC207~209	4	LC4081B	IC
IC210	1	M888505-558M	IC
IC211	1	LC4011B	IC
IC212	1	YM3404B	IC
IC301	1	PCN56P	IC
IC302	1	MN4053B	IC
IC303~304	2	UPC4570HA-1	IC
IC305	1	UPD06360C	IC
IC401	1	UPC4570HA-1	IC
IC451	1	UPC4570C-1	IC
IC452	1	TC9153AP	IC
IC453	1	UPC4570C-1	IC
IC601	1	AN7810F	IC
IC602	1	AN7910F	IC
IC603	1	UPC7805HF	IC
IC604	1	UPC7905HF	IC
IC605	1	UPC7812HF	IC
IC606	1	UPC7912HF	IC
IC607	1	UPC7808HF	IC
ZD101,102,	4	ZD50-057	ZENER DIODE,1/2W,5.7V
601,602			
ZD603	1	ZD50-107	ZENER DIODE,1/2W,10.7V
<u>CAPACITORS</u>			
C101	1	NS-25TW100M	ELECTROLYTIC CAPACITOR
C102	1	HC105JZF473Z	CERAMIC CAPACITOR
C103,104	2	MY-50VS182J	MYLAR CAPACITOR
C105	1	MY-50VS683J	MYLAR CAPACITOR
C106	1	NP-50TW833M	ELECTROLYTIC CAPACITOR
C107	1	NP-50TW22M	ELECTROLYTIC CAPACITOR
C108	1	NS-25TW100M	ELECTROLYTIC CAPACITOR
C109	1	NS-10TW220M	ELECTROLYTIC CAPACITOR
C110	1	NS-50TW22M	ELECTROLYTIC CAPACITOR
C111	1	CC455L1H270J	CERAMIC CAPACITOR
C112	1	NS-25TW100M	ELECTROLYTIC CAPACITOR
C116	1	NS-16TW330M	ELECTROLYTIC CAPACITOR
C117	1	HY-50VS152J	MYLAR CAPACITOR
C118	1	HY-50VS472J	MYLAR CAPACITOR
C119	1	CC455L1H221K	CERAMIC CAPACITOR
C120	1	NS-10TW470M	ELECTROLYTIC CAPACITOR
C121	1	HY-50VS473J	MYLAR CAPACITOR
C122	1	HY-50VS682J	MYLAR CAPACITOR
C123	1	ECQV1H154JZ	METALLIZED FILM CAPACITOR
C124	1	HY-50VS102J	MYLAR CAPACITOR
C125	1	CC455L1H221K	CERAMIC CAPACITOR
C126,127	2	MY-50VS103J	MYLAR CAPACITOR

REF. NO.	Q'TY	PART NO.	DESCRIPTION
<u>REF. NO.</u>			
C128	1	NP-50VS100M	ELECTROLYTIC CAPACITOR
C129	1	HY-50VS152J	MYLAR CAPACITOR
C130,131	2	NS-50TW100M	ELECTROLYTIC CAPACITOR
C132	1	NS-16TW221M	ELECTROLYTIC CAPACITOR
C133	1	NS-25TW100M	ELECTROLYTIC CAPACITOR
C134	1	HE70SJYF037	CERAMIC CAPACITOR
C135,136	2	HC75SJZF223Z	CERAMIC CAPACITOR
C137~138	2	NS-10TW101M	ELECTROLYTIC CAPACITOR
C201	1	ECQV1H104JZ	METALLIZED FILM CAPACITOR
C202	1	HE405JSL470J	CERAMIC CAPACITOR
C204	1	HC105JZF473Z	CERAMIC CAPACITOR
C205	1	HY-50VS473J	MYLAR CAPACITOR
C206	1	MY-50VS103J	MYLAR CAPACITOR
C207	1	ECQF-147JZ	POLYESTER FILM CAPACITOR
C209	1	ECQF-1221JZ	POLYESTER FILM CAPACITOR
C210	1	HY-50VS473J	MYLAR CAPACITOR
C211	1	HY-50VS102J	MYLAR CAPACITOR
C212	1	CC455L1H101J	CERAMIC CAPACITOR
C213	1	NS-25TW100M	ELECTROLYTIC CAPACITOR
C214	1	HY-50VS103J	MYLAR CAPACITOR
C215	1	ECQV1H104JZ	METALLIZED FILM CAPACITOR
C216	1	HY-50VS122J	MYLAR CAPACITOR
C218	1	ECQV1H247JZ	METALLIZED FILM CAPACITOR
C219	1	NS-25TW47R7	ELECTROLYTIC CAPACITOR
C220	1	NS-25TW470M	ELECTROLYTIC CAPACITOR
C221~222	2	CC455H100J	CERAMIC CAPACITOR
C223	1	NS-25TW100M	ELECTROLYTIC CAPACITOR
C224~228	5	HC105JZF473Z	CERAMIC CAPACITOR
C229	1	NS-25TW100M	ELECTROLYTIC CAPACITOR
C230	1	HC105JZF473Z	CERAMIC CAPACITOR
C231	1	CK45F1H473Z	CERAMIC CAPACITOR
C232	1	CC455L1H100D	CERAMIC CAPACITOR
C301,302	2	CO15P1H471GZK	POLYESTER FILM CAPACITOR
C303,304	2	ECOM1H683JY	POLYESTER FILM CAPACITOR
C305,306	2	ECOP1H222GZ	POLYESTER FILM CAPACITOR
C307,308	2	CO15P1H471GZK	POLYESTER FILM CAPACITOR
C309,310	2	ECQV1H104JZ	METALLIZED FILM CAPACITOR
C311,312	2	NP-25TW470M-KF	ELECTROLYTIC CAPACITOR
C315	1	NS-25TW47R7	ELECTROLYTIC CAPACITOR
C316	1	NS-10TW221M	ELECTROLYTIC CAPACITOR
C319,320	2	NS-25TW47R7M	ELECTROLYTIC CAPACITOR
C321,322	2	HC105JZF473Z	CERAMIC CAPACITOR
C325	2	HY-50VS472J	MYLAR CAPACITOR
C325	1	CK45F1H473Z	CERAMIC CAPACITOR
C401,402	2	NP-25TW220M	ELECTROLYTIC CAPACITOR
C403~406	4	NS-16TW221M	ELECTROLYTIC CAPACITOR
C407,408	2	NS-50TW33M	ELECTROLYTIC CAPACITOR
C409,410	2	ECQV1H104JZ	METALLIZED FILM CAPACITOR
C411~414	4	NP-25TW220M	ELECTROLYTIC CAPACITOR
C451~454	4	NS-50TW100M	ELECTROLYTIC CAPACITOR
C455,456	2	NS-10TW101M	ELECTROLYTIC CAPACITOR
C457~460	4	NS-50TW100M	ELECTROLYTIC CAPACITOR
C461,462	2	NP-25TW220M	ELECTROLYTIC CAPACITOR
C465,466	2	HY-50VS472J	MYLAR CAPACITOR
C467	1	NS-25TW2R2M	ELECTROLYTIC CAPACITOR
C468	1	UVX1H010KA1TA	ELECTROLYTIC CAPACITOR
C469	1	UVX1H100KA1TA	ELECTROLYTIC CAPACITOR
C471,472	2	NS-25TW100M	ELECTROLYTIC CAPACITOR
C601	1	NS-25TW222M-KF	ELECTROLYTIC CAPACITOR
C602	1	NS-16TW101M	ELECTROLYTIC CAPACITOR
C603	1	NS-25TW100M	ELECTROLYTIC CAPACITOR
C604	1	NS-25TW222M-KF	ELECTROLYTIC CAPACITOR
C605,606	2	NS-16TW101M	ELECTROLYTIC CAPACITOR
C607	1	NS-25TW222M-KF	ELECTROLYTIC CAPACITOR
C608	1		

HEADPHONE PCB ASSY

REF. NO.	Q'TY	PART NO.	DESCRIPTION
P.C.B. BOARD 1RE 1	1	HP-K032A	PRINTED CIRCUIT BOARD
SEMICONDUCTORS 0503,504	2	2SC2878-A+B	TRANSISTOR
IC501	1	MS216L	IC
CAPACITORS C501,502 C503,504 C505,506 C507,508 C509,510 C511	2	NS-50TW100M NS-10TW470M HE605JSL151J NS-50TW100M HE70SJYF103Z HC10SJZF473Z	ELECTROLYTIC CAPACITOR ELECTROLYTIC CAPACITOR CERAMIC CAPACITOR ELECTROLYTIC CAPACITOR CERAMIC CAPACITOR CERAMIC CAPACITOR
RESISTORS R505,506 R507,508 R509,512 R513,514 R515,516 R517,518	2	KA16ST224J KA16ST103J KA16ST102J KA16ST121J KA16ST131J KA16ST682J	CARBON RESISTOR CARBON RESISTOR CARBON RESISTOR CARBON RESISTOR CARBON RESISTOR CARBON RESISTOR
MISCELLANEOUS HP501	1	HLJ4308-01-308 H.P. JACK	
MC502	1	MT-22A07F-K063	MICRO SOCKET ASS'Y
TU001~004	4	U9-#188005	UL TYPE TUBE
1RE26 1RE27 1RE28 1RE29	2 2 1 3	E075 E100 E150 E175	JAMP WIRE JAMP WIRE JAMP WIRE JAMP WIRE

OPERATION PCB ASSY

REF. NO.	Q'TY	PART NO.	DESCRIPTION
P.C.B. BOARD 1RE 1	1	OPE-K032A	PRINTED CIRCUIT BOARD
SEMICONDUCTORS 0701~703	3	1S5133	DIODE
LD701 LD702,703 LD704~706 LD707	1 2 3 1	LN342GP LN842RP(V) LN442YP LN342GP	LED LED LED LED
CAPACITORS C701	1	SS-6R3TW101M	ELECTROLYTIC CAPACITOR
RESISTORS R701 R702~704	1 3	KA16ST221J KA16ST151J	CARBON RESISTOR CARBON RESISTOR
SWITCHES S701 S702 S703~704 S705 S706~708 S709~710 S711~713	1 1 2 1 3 2 3	SKHHQV SKHHPK SKHHQV SKHHPK SKHHQV SKHHPK SKHHQV	TACT SWITCH TACT SWITCH TACT SWITCH TACT SWITCH TACT SWITCH TACT SWITCH TACT SWITCH
MISCELLANEOUS BX701	1	BX1387	REMOTE SIGNAL RECEIVING UNIT
HC701 HC702 HC703	1 1 1	MK-ILS075-K054 MK-ILS035-K055 MK-ILS095-K035	MICRO SOCKET ASS'Y MICRO SOCKET ASS'Y MICRO SOCKET ASS'Y
1RE23 1RE29 1RE30	6 6 2	E050 E100 E150	JAMP WIRE JAMP WIRE JAMP WIRE

VOLUME PCB ASSY

REF. NO.	Q'TY	PART NO.	DESCRIPTION
P.C.B. BOARD 20E 1	1	VR-K032A	PRINTED CIRCUIT BOARD
SEMICONDUCTORS 0501~502	2	2SC2878-A+B	TRANSISTOR
RESISTORS R501,502 R503,504	2	KA16ST102J KA16ST682J	CARBON RESISTOR CARBON RESISTOR
VR501	1	VBV16-503A20K4	ROTARY POTENTIOMETER
HISCELLANEOUS MC501 20E10	1 1	MT-22A07F-K067 E125	MICRO SOCKET ASS'Y JAMP WIRE

LED PCB ASSY

REF. NO.	Q'TY	PART NO.	DESCRIPTION
P.C.B. BOARD 20E12	1	LED-K032A	PRINTED CIRCUIT BOARD
SEMICONDUCTORS LD801 LD802,803	1 2	SL9406-20 LN513RKS	LED LED
RESISTORS R801	1	KA16ST220J	CARBON RESISTOR
MISCELLANEOUS MC601 MC802	1 1	MC-172677-K039 MC-172677-K053	MICRO SOCKET ASS'Y MICRO SOCKET ASS'Y

POWER SUPPLY PCB ASSY

REF. NO.	Q'TY	PART NO.	DESCRIPTION
P.C. BOARD 21E 1	1	PS-K036	PRINTED CIRCUIT BOARD
CAPACITORS △ C901	1	ECQU2A103MN	METALLIZED FILM CAPACITOR
COILS △ L901,902	2	180016	CHOKE
SWITCHES △ S901	1	ESB8215V	POWER SWITCH
MISCELLANEOUS EL901,902 EL903~905	2 3	59854795 S-001P	GND LUG GND LUG
△ FU901	1	FU-524014ST	FUSE
△ 21E14 △ 21E17 △ 21E23	2 1 1	23165102-BB-C 820633 BK4123-401	FUSE HOLDER CAPACITOR BOOT LABEL FUSE

OTHER PARTS

REF. NO.	Q'TY	PART NO.	DESCRIPTION
MISCELLANEOUS J013	1	0075260806-C-C	SOLDER-PLATED WIRE
ZM28	2	VJR-3	SNAKE LUG
3M 2 3M 5, M29, M30	1 6	BK4151 N45335	MASTER CARTON LABEL, SERIAL NO.
5M23	2	TPM+30X08-B	TAP SCREW P, ROUND HEAD, B
MC101 MC102 MC103 MC104 MC105 MC202	1 1 1 1 1 1	MZ-PHR09-K058 MZ-PHR06-K057 MK-ILS035-K075 MT-22A02F-K065 M84-02-300SA MT-22A03F-K066	MICRO SOCKET ASS'Y MICRO SOCKET ASS'Y MICRO SOCKET ASS'Y MICRO SOCKET ASS'Y MICRO SOCKET ASS'Y MICRO SOCKET ASS'Y

Classify Parts List

A : USA B : U.K. C : EUROPE & OTHERS C2: G.P.M.
 A1: CANADA B1: AUSTRALIA/N.Z. C1: W.GERMANY

Ref.No.	Description	A	A1	B	B1	C/C1	C2
MAIN UNIT Section							
1M18	REAR PANEL	BK2037	BK2037	BK2037-1	BK2037-1	BK2037-2	BK2037-2
3M10	CAUTION SHEET, POLARIZED PLUG	N44687	N44687	Nil	Nil	Nil	Nil
3M11	LABEL, FUSE	N44525	N44525	Nil	Nil	Nil	Nil
3M13	CONVERSION PLUG	Nil	Nil	Nil	Nil	S-16115#01	
3M14	FDA LABEL LASER CAUTION	BK4082A	BK4082A	Nil	Nil	Nil	Nil
3M14-1	LABEL (LASER MARK)	Nil	Nil	N44838	N44838	N44838	N44838
3M15	CSA LABEL LASER CAUTION	BK4081A	BK4081A	Nil	Nil	Nil	Nil
3M15-1	LABEL (LASER CAUTION)	Nil	Nil	N44839	N44839	N44839	N44839
3M16	LABEL (CLASS 1 LASER PRODUCT)	Nil	Nil	N44837	N44837	N44837	N44837
3M18	TAG (AC CORD)	Nil	Nil	N41117	Nil	Nil	Nil
3M19	STICKER WARNING	Nil	Nil	N41994	Nil	Nil	Nil
3M21	POLYETHYLENE BAG (UNIT)	N41886-2	N41886-2	N41886-H-2	N41886-2	N41886-2	N41886-2
3M23	CARD, WARRANTY REGISTRATION	NAD-WC2A	NAD-WC2A	Nil	Nil	Nil	Nil
3M25	LABEL, UL	N4934A	N4934A	Nil	Nil	Nil	Nil
3M26	NON-WARRANTY CARD	LEN-200	LEN-200	Nil	Nil	Nil	Nil
3M26-1	SAFETY INSTRUCTION SHEET	BK3035	BK3035	Nil	Nil	Nil	Nil
3M27	CARD, WARRANTY	LEN-201	LEN-201	Nil	Nil	Nil	Nil
3M28	LABEL, CSA COMPACT DISC	BK4142	BK4142	Nil	Nil	Nil	Nil
△ 22E16	LINE CORD	ACC-033E3-4EC1	ACC-033E3-4EC1	ACC-03D3-4EC4	ACC-03D3-4EC1	ACC-005D3-4EC1	ACC-005D3-4EC1
22E19	CORD STOPPER	SR-4N-4	SR-4N-4	SR-5N-4	SR-4N-4	SR-4N-4	SR-4N-4
△ PT001	POWER TRANSFORMER	NPT-K0104	NPT-K0104	NPT-K0105	NPT-K0105	NPT-K0105	NPT-K0105
POWER SUPPLY PCB Section							
△ C901	METALLIZED FILM CAPACITOR	ECQU2A103MN	ECQU2A103MN	ECQU2A103MF	ECQU2A103MF	ECQU2A103MF	ECQU2A103MF
△ FU901	FUSE	FU-524014ST	FU-524014ST	FU-522017T	FU-522017T	FU-522017T	FU-522017T
TU013,014	UL TYPE TUBE	Nil	Nil	U9-#01B02	U9-#01B02	U9-#01B02	U9-#01B02
△ 21E17	CAPACITOR BOOT	820633	820633	821033	821033	821033	821033
△ 21E23	LABEL FUSE	BK4123-401	BK4123-401	Nil	Nil	Nil	Nil

Capacitors Description

Type	Voltage	Value	Tolerance	Type	Voltage	Value	Tolerance	Type	Voltage	Value	Tolerance

<tbl_r cells="12" ix="1" maxcspan="1" maxrspan="1" usedcols="

THE DIFFERENCE OF PICK-UP HEAD

This model is in use the pick-up head of either Part No. is MLP-10 or MLP-10F2. In the case that you exchange the pick-up head with new one for the replacement, please use MLP-10F2 instead of MLP-10. With this modification, the values of some electrical parts and etc. shall be required to be changed.

After read **Cautions on Replacement of Pick-up** on page 4, you shall be exchanged the pick-up head.


1. Please exchange of parts refer to the below table and figure.

- Delete resistor R189.
- Exchange resistor R190 for the jump wire and short-circuit.
- The other parts exchange Part No. column A for B according as the below table.

A: Serial No.80400038~ 80400512 (Except Serial No.80400139 and 80400472)
 B: Serial No.80400513~ (Include Serial No.80400139 and 80400472)

Ref. No.	Description	Part No.	
		A	B
—	PICK UP HEAD	MLP-10	MLP-10F2
D102	DIODE	1SS133	MA27WA
C103, 104	MYLAR CAPACITOR	MY-50VS222J	MY-50VS182J
R109	CARBON RESISTOR	KA16ST103J	KA16ST153J
R119	CARBON RESISTOR	KA16ST394J	KA16ST684J
R123	CARBON RESISTOR	KA16ST184J	KA16ST474J
R124	METAL FILM RESISTOR	MF16ST203F	MF16ST153F
R125	CARBON RESISTOR	KA16ST124J	KA16ST274J
R128	CARBON RESISTOR	KA16ST103J	KA16ST223J
R133	CARBON RESISTOR	KA16ST103J	KA16ST223J
R151	CARBON RESISTOR	KA16ST104J	KA16ST823J
R189	CARBON RESISTOR	KA16ST181J	Nil
R190	CARBON RESISTOR	KA16ST1R0J	Short

MAIN PCB ASSY



2. The difference of Adjustment value (Tracking Gain) refers to the following.

Pick-up head : MLP-10

Rating : ETE = (EQ +15 dB) ±3 dB

Pick-up head : MLP-10F2

Rating : ETE = (EQ +11 dB) ±3 dB

SERVICE MANUAL

5100
COMPACT DISC PLAYER

SM-K040 8808
© 1987 BY NAD PRINTED IN JAPAN

NAD ELECTRONICS
BOSTON/LONDON