

SPANNUNGS- UND STROMTABELLE

MIT ZULÄSSIGEN MESSGRENZEN

Röhre	Verwendung	Anoden- spannung	Anoden- strom	Hilfs- oder Schirm- gittersp.	Heiz- spannung	Mess- punkte
L2 : E442	Hochfr.	135-160 V.	0.5-1.5 mA.	70- 90 V.	3.7-3.9 V.	1-2-3-4
L3 : E424	Audion	70- 90 V.	3.4-6.1 mA.	—	3.7-3.9 V.	5-6-7
L4 : B443	Niederfr.	125-160 V.	12-16 mA.	155-180 V.	3.7-3.9 V.	8-9-10-11-12
L1 : 506	Gleichr.	2×175 V.~	—	—	3.7-3.9 V.	—

WIDERSTÄNDE			
Bezeich- nung	Wert	Code- Nr.	Preis
R1 ==	220 Ohm	25.717.29	/.-
R2 ==	35 Ohm	25.716.96	/.-
R3 ==	0,6 Megohm	25.722.40	/.-
R4 ==	0,1 Megohm	25.722.71	/.-
R5 ==	1 Megohm	25.722.73	/.-
R6 ==	6000 Ohm	25.716.94	/.-
R7 ==	15000 Ohm		
R8 ==	120 Ohm	25.716.93	/.-
R9 ==	120 Ohm		
R12 ==	1 Megohm	25.722.73	/.-

KONDENSATOREN			
Bezeich- nung	Wert	Code- Nr.	Preis
C1 ==	4 µF.	25.112.30	/8.-
C2 ==	3 µF.		
C3 ==	1 µF.		
C4 ==	1 µF.		
C5 ==	0.5 µF.		
C6 ==	0.5 µF.		
C7 ==	20 µµF.	25.113.03	/.-
C8 ==	550 µµF.	25.127.34	/4.-
C9 ==	550 µµF.		
C10 ==	160 µµF.	25.113.08	/.-
C11 ==	1600 µµF.	25.112.67	/.-
C12 ==	500 µµF.	25.113.07	/.-
C13 ==	500 µµF.	25.113.07	/.-
C14 ==	500 µµF.	25.113.07	/.-
C16 ==	64 µµF.	25.112.79	/.-
	od. 100 µµF.	25.112.63	/.-