




Circuits des Résistances

9	13	23	38	43	48	53		V	A	61	N1	N2					
	100	100	200	135	275	220		210	0	350	0	0					
10	16	17	19	27	28	45	47	57									
	180	180	135	180	440	400	180	440									
11	11	12	15	21	22	25	31	32	41	42	51	52	67	68	L	S	
	375	245	375	375	375	375	375	375	280	290	400	200					
12	P	35															
	5	5															

Circuits des Capacités

9	11	12	15	18	21	22	25	28	31	32	41	42	45	51	52	57	61	62	67	S			
	475	320	340	475	160	350	475	475	490	475	480	475	15	475									
10	16	17	27	47	58	68	L																
	230	230	230	230	230	300	230																
11	13	23																					
	245	290																					
12	19	38	43	48	53	A	V																
	400	235		160	0	200																	

Placer le commutateur de longueurs d'ondes sur G.O.
 " le volume contrôle au maximum

Les mesures seront faites par rapport à la "Terre" (pôle négatif du pupitre)