


Circuits des Résistances

9	13	23	38	43	47	48	53	58	P										
	70	100	160	140	190	280	200	500	210										
10	17	27	45	A															
	260	270	420	180															
11	15	18	25	28	57	L													
	400	440	410	445	380	380													
12	11	21	31	32	35	41	42	51	52	55	U	N1	N2						
	5	5	5	0	5	5	0	0	0	500	500								

Circuits des Capacités

9	45	57	61	62															
	490	490	490	490															
10	15	18	25	27	67	68	S												
	400	390	400	100	390	390	210												
11	17	47	A																
	330	240	160																
12	13	23	38	43	48	53	P												
	60	40	110	180	275	180	200												

Placer le commutateur de longueurs d'ondes sur G.O.
le volume contrôle au maximum

Les mesures seront faites par rapport à la "terre" (pôle négatif du pupitre)

Pour le contrôle de P mettre le commutateur de λ sur P.V.