



NOTES:

1. UNLESS NOTED ALL RESISTANCES ARE IN OHMS, ALL RESISTORS ARE 1/2 WATT, 10%. ALL CAPACITANCES ARE IN MICROMICROFARADS. ALL INDUCTANCES ARE IN MICRohenRIES
2. VOLTAGE MEASUREMENTS ABOVE THE LINE AND RESISTANCE MEASUREMENTS ARE SHOWN BELOW THE LINE. S101 IS IN "OFF" POSITION FOR ALL RESISTANCE MEASUREMENTS.
3. VOLTAGE APPROX. 15% LESS FOR THE KX-100 & KX-110.

FIGURE: 7-2 KY-90 SCHEMATIC DIAGRAM